



Pushbutton sensor 4.95, 24 V, 2-gang



| Specification | Order No. | Packing unit | £/piece without VAT | PS | EAN |
|--|-----------|--------------|------------------------|----|---------------|
|  white | 5052 003 | 1 | 83.39 | 02 | 4010337074946 |
|  anthracite | 5052 028 | 1 | 83.39 | 02 | 4010337074953 |

Features

- Pushbutton sensor 4.95 for connection to 24 V control systems.
- Operating surface made of high-quality three-millimetre thick real material (glass, stainless steel, aluminium).
- Two white status LEDs per rocker.
- Measurement of the room temperature with integrated temperature sensor (PT1000).

Technical data

| | |
|------------------------|----------------------|
| Button | |
| - Rated voltage: | AC/DC 24 V SELV |
| - Current capacity: | 20 mA per button |
| - Output resistance: | 880 Ω |
| LED | |
| - Rated voltage: | DC 24 V SELV |
| - Current consumption: | approx. 1 mA per LED |
| Temperature sensor: | PT1000, class B |
| Protection class: | III |
| Installation depth: | 16 mm |
| Ambient temperature: | -5 °C to +45 °C |

Notes

- Suitable for SELV circuits only.
 - Professional inscription by the Gira inscription service www.marking.gira.com.
 - The pushbutton sensor is delivered with a program-neutral start-up rocker. The suitable rocker set for the switch range must be ordered separately.
-