



## Pushbutton sensor 4.95, 24 V 4-gang



Specification	Order No.	Packing unit	£/piece without VAT	PS	EAN
 white	5054 003	1	94.49	02	4010337074922
 anthracite	5054 028	1	94.49	02	4010337074939

### Features

- Pushbutton sensor 4.95 for connection to 24 V control systems.
- Operating surface made of high-quality three-millimetre thick real material (glass, stainless steel, aluminium).
- Two white status LEDs per rocker.
- Measurement of the room temperature with integrated temperature sensor (PT1000).

### Technical data

<b>Button</b>	
- Rated voltage:	AC/DC 24 V SELV
- Current capacity:	20 mA per button
- Output resistance:	880 Ω
<b>LED</b>	
- Rated voltage:	DC 24 V SELV
- Current consumption:	approx. 1 mA per LED
Temperature sensor:	PT1000, class B
Protection class:	III
Installation depth:	16 mm
Ambient temperature:	-5 °C to +45 °C

## Notes

- Suitable for SELV circuits only.
  - Professional inscription by the Gira inscription service [www.marking.gira.com](http://www.marking.gira.com).
  - The pushbutton sensor is delivered with a program-neutral start-up rocker. The suitable rocker set for the switch range must be ordered separately.
-