


Bus coupler button WP SM, 1-gang with control window and single-point operation for KNX



| Specification | Order No. | Packing unit | £/piece without VAT | PS | EAN |
|---|-----------|--------------|------------------------|----|---------------|
|  grey | 5151 30 | 1 | 82.80 | 06 | 4010337500063 |

The bus coupler button is the interface between the KNX system and the user.

Features

Button function

- Switching, dimming, blind, value transmitter 1-byte, and scene auxiliary unit.
- Switching function: Command for pressing and releasing the buttons can be parameterised (ON, OFF, CHANGE, no reaction).
- Dimming function: Command for pressing the buttons can be parameterised (Brighter-ON, Darker-OFF, Brighter or Darker-CHANGE, Brighter-CHANGE, Darker-CHANGE, no reaction).
- Blind function: Command for pressing the buttons can be parameterised (UP, DOWN, no reaction).
- Value transmitter 1-byte function: Mode of operation can be configured.
- Scene auxiliary unit function: Mode of operation can be configured (with or without block function for pressing and holding a button).
- Single-point operation (rocker at an angle) only allows one-sided (bottom) rocker operation.
- Bus coupler button in the water-protected surface-mounted system (IP44).
- Functions of the status LED: Red LED can either be used as an orientation light, actuation display, or status display.

Technical data

| | |
|----------------------|----------------------------------|
| KNX connection: | Connection and junction terminal |
| Protection class: | III |
| Ambient temperature: | -25 °C to +55 °C |
| Relative humidity: | 5 to 93 % (without condensation) |

Scope of supply

- Connection and junction terminal for KNX included with delivery.
-