


## eNet wireless control unit 1 – 10 V, 1-gang Mini



| Specification  | Order No. | Packing unit | £/piece<br>without VAT | PS | EAN           |
|--|-----------|--------------|------------------------|----|---------------|
|  | 5421 00   | 1/5          | 134.32                 | 42 | 4010337774174 |

### Features

- The eNet wireless control unit enables the switching and brightness setting of lights with 1 - 10 V interface.
- Switch-on and minimum brightness can be saved.
- Scene operation.
- Status display of the 1 - 10 V devices by LED.
- Status feedback to eNet radio transmitter.

Can be set with eNet server:

- Maximum brightness.
- Dimming speed.
- Delay time.
- Switch-on/off delay.
- Dimming ramp up/down.
- Switch-off pre-warning.
- Permanent-on, permanent-off.
- Hotel function.
- Light control.
- Repeater function.
- Localisation of the device.

### Technical data

|                      |                    |
|----------------------|--------------------|
| Rated voltage:       | AC 230 V, 50/60 Hz |
| Standby:             | max. 0.5 W         |
| Ambient temperature: | -25 °C to +70 °C   |
| Control current:     | max. 50 mA         |
| Switching current    |                    |
| - Ohmic load:        | 6 A                |
| - Fluorescent lamps: | 3 AX               |
| Connected load       |                    |
| - Ohmic load:        | 1380 W             |

Illustrations are similar and may deviate from originals.  
Prices valid for United Kingdom with prices valid 01/25.

|                           |                    |
|---------------------------|--------------------|
| - Capacitive load:        | 690 VA (560 µF)    |
| Connection cross section: | Max. 4 mm²         |
| Wireless frequency:       | 868.0 to 868.6 MHz |
| Range (free field):       | approx. 100 m      |

---

## Notes

- Mounting in device box, surface-mounted housing or in installation adapter.

---

## Dimensions in mm

Ø 53      H 28

---