


## eNet wireless switching/momentary-contact actuator 1-gang, Mini zero-voltage



Specification	Order No.	Packing unit	PS	EAN
	5424 00	1/5	42	4010337774211

### Features

- The eNet radio switching/momentary-contact actuator enables switching of lighting.
- Operating modes: Switching actuator or momentary-contact actuator.
- Status feedback to eNet radio transmitter.
- Scene operation.
- Operating mode buttons: Relay contact stays closed as long as telegrams are being received (max. 60 seconds).

Can be set with eNet server:

- Flashing function.
- Delay time.
- Switch-on/off delay.
- Switch-off pre-warning.
- Minimum switching repeat time.
- Permanent-on, permanent-off.
- Repeater function.
- Localisation of the device.

### Technical data

Rated voltage:	AC 230 V, 50/60 Hz
Standby:	max. 0.5 W
Ambient temperature:	-25 °C to +70 °C
Breaking capacity 230 V AC:	16 A/AC1
Connected load	
- Light bulbs:	2300 W
- HV halogen lamps:	2000 W
- Wound electronic transformer:	1000 VA
- Tronic transformer:	1500 W
- Fluorescent lamps, uncompensated:	920 VA
- LED lights:	typically 500 W

Illustrations are similar and may deviate from originals.

- Compact fluorescent lamp:	typically 500 W
- Capacitive load:	690 VA (560 µF)
Connection cross section:	Max. 4 mm <sup>2</sup>
Wireless frequency:	868.0 to 868.6 MHz
Range (free field):	approx. 100 m

---

## Notes

- Mounting in device box, surface-mounted housing or in installation adapter.
- 

## Dimensions in mm

Ø 53      H 28

---