


eNet Radio blind actuator, 1-gang Mini



| Specification | Order No. | Packing unit | PS | EAN |
|---|-----------|--------------|----|---------------|
|  | 5427 00 | 1/5 | 42 | 4010337774235 |

Features

- The eNet wireless blind actuator enables the control of electrically operated hangings such as blinds, shutters and awnings.
- Positioning of blinds and slats using scene call-up.
- Positions for sun protection and twilight can be saved.
- Status feedback to eNet radio transmitter.
- Hanging travel time can be saved.
- Slat adjustment time can be saved.

Can be set with eNet server:

- Adjustment time when changing directions.
- Direction of travel can be inverted (e.g. for roof windows).
- Position for solar protection, twilight, lock-out protection, and wind alarms.
- Behaviour after mains power failure.
- Repeater function.
- Localisation of the device.

Technical data

| | |
|---------------------------|------------------------|
| Rated voltage: | AC 230 V, 50/60 Hz |
| Standby: | max. 0.5 W |
| Ambient temperature: | -25 °C to +70 °C |
| Connected load of motors: | 1000 W |
| Connection cross section: | Max. 4 mm ² |
| Wireless frequency: | 868.0 to 868.6 MHz |
| Range (free field): | approx. 100 m |

Notes

- Mounting in device box, surface-mounted housing or in installation adapter.

Dimensions in mm

Ø 53

H 28
