


eNet wireless blind actuator, 1-gang



Specification	Order No.	Packing unit	£/piece without VAT	PS	EAN
 DRA	5437 00	1	130.63	42	4010337774297

Features

- The eNet wireless blind actuator receives telegrams for controlling electrically operated hangings such as blinds, shutters and awnings from the eNet wireless receiver module or eNet server via a data line.
- Positioning of blinds and slats using scene call-up.
- Positions for sun protection and twilight can be saved.
- Threshold value scenes for solar protection, twilight and wind alarms.
- Status feedback to eNet radio transmitter.
- Hanging travel time can be saved.
- Slat adjustment time can be saved.

Can be set with eNet server:

- Adjustment time when changing directions.
- Direction of travel can be inverted (e.g. for roof windows).
- Position for solar protection, twilight, lock-out protection, and wind alarms.

Technical data

Rated voltage:	AC 230 V, 50/60 Hz
Standby:	max. 0.2 W
Ambient temperature:	-5 °C to +45 °C
Connected load of motors:	1000 W
Connection cross section:	Max. 4 mm ²

Notes

- An eNet wireless receiver module or an eNet server is required to operate this DIN rail adapter.

Dimensions

Modular width (MW): 2
