










eNet wireless operating top unit arrow symbols



| Specification | Order No. | Packing unit | PS | EAN |
|---|-----------|--------------|----|---------------|
|  cream white glossy | 5494 01 | 1/5 | 42 | 4010337104667 |
|  pure white glossy | 5494 03 | 1/5 | 42 | 4010337104650 |
|  pure white matt | 5494 27 | 1/5 | 42 | 4010337104643 |
|  anthracite | 5494 28 | 1/5 | 42 | 4010337104636 |
|  colour aluminium | 5494 26 | 1/5 | 42 | 4010337104629 |
|  black matt | 5494 005 | 1/5 | 42 | 4010337104605 |
|  grey matt | 5494 015 | 1/5 | 42 | 4010337104599 |
|  stainless steel | 5494 600 | 1/5 | 42 | 4010337104612 |

Features

- Operation on switching, dimming or blind insert or 3-wire auxiliary insert from System 3000.
- Manual, wireless and time-controlled operation of e.g. blinds, shutters, awnings, lighting or fans.
- Transmitter for wireless transmission of switching, dimming and blind commands.
- Adjustable night mode. Status LED and function LED are not lit up continuously.
- Status feedback to wireless transmitter.
- Status display with LED.
- Evaluation of auxiliary inputs.

Functions in combination with blind insert:

- Positioning of hangings via scene call-up.
- Position for sun protection and twilight.
- Runtime and ventilation position of the hanging can be saved.

Functions in combination with light insert:

- Scene operation possible.
- Switch-on brightness can be permanently stored when combined with dimming insert.

Functions in combination with 3-wire auxiliary unit:

- Power-supplied eNet transmitter.
- Lighting control.
- Shading control.

Adjustable with eNet server version 2.3 and higher (depending on the insert):

- Fully encrypted wireless transmission (AES-CCM).
- Deactivate auxiliary unit evaluation.
- Operation locks.
- Reversal time adjustable for blinds, shutters and awnings.
- Direction of travel can be inverted.
- Position for sun protection, twilight, lock-out protection and wind alarm.
- Maximum brightness, minimum brightness and dimming speed adjustable.
- Function of the status LED can be set as status LED/actuation display.
- Delay time.
- Switch-on/off delay.
- Dimming ramp up/down.
- Switch-off pre-warning.
- Permanent-on, permanent-off.
- Hotel function.
- Light control.
- Repeater function.
- Device software update.

Technical data

| | |
|----------------------|--------------------|
| Ambient temperature: | -5 °C to +45 °C |
| Wireless frequency: | 868.0 to 868.6 MHz |
| Range (free field): | approx. 100 m |

Notes

- The range can be reduced when using a metal top unit and/or metal cover frames.
 - Radio approval is valid for EU and EFTA countries.
-