






System 106 call-button module 1-gang



Specification	Order No.	Packing unit	£/piece without VAT	PS	EAN
 stainless steel	5531 920	1	174.83	20	4010337022626
 aluminium	5531 926	1	163.07	20	4010337022619
 traffic white (laquered)	5531 902	1	147.64	20	4010337022602
 stainless steel V4A	5531 914	1	228.92	20	4010337091967
 bronze	5531 921	1	228.92	20	4010337100867
 black matt	5531 925	1	228.92	20	4010337100706

The Gira System 106 is an installation system made of metal in a puristic and elegant frameless design, based on basic measurements of 106.5 × 106.5 mm. With the modular door intercom in Gira System 106, hospitality begins even before you reach the front door. All the functions are presented in a harmonious overall appearance, from the call button module, intercom module, and camera module, up to the info and blank module. In the dark, backlit call buttons with inscription space ensure good legibility and an attractive appearance.

Individually adaptable modular system

The System 106 can be used in family homes or apartment buildings, as well as in office buildings, industrial properties, and hotels. The modular design enables the system's size, design, and functionality to be individually adapted to the respective requirements. Expansions and changes are possible at any time by easily exchanging the modules.

With this system, it is also possible to exchange the fronts only. This means that the appearance of the system can be changed from e.g. traffic white to a stainless steel surface at a later stage, without having to exchange the electronic units.

High-quality materials

The modules are frameless with design fronts made of genuine materials, available in two brushed stainless steel versions (V2A and V4A), anodised aluminium C-0, and a metal alloy lacquered in traffic white (RAL 9016): all robust materials which ensure durability. The camera and DIN 18040 display module feature a black glass cover.

Easy and phased installation

The system can be installed in phases, in parallel to the progress of building work. In this way, it is possible to initially install only the lower part of a surface-mounted housing during construction of the shell; cables and modules can then be added when they are needed.

Individual inscription options

Call button modules and info modules can be labelled individually via the Gira inscription service.

Features

- Easy-to-use, vandal-proof, and scratch-resistant call buttons.
- Function changes, e.g from 2-gang to 4-gang, can be easily implemented by replacing the buttons.
- Various inscription options possible.

Technical data

Power supply

- System: via flat ribbon cable, 10-pole

Power consumption

- Maximum: 160 mW

- Stand-by mode: 14 mW

Connections

- System: 2 x connector strip

Ambient temperature: -25 °C to +70 °C

Protection class: IP54

Notes

- Professional inscription by the Gira inscription service www.beschriftung.gira.de.

Dimensions in mm

B 106,5

H 106,5

T 28,7