










## Régulateur de bâtiment avec interface de bouton-poussoir 4x pour KNX



Spécification	Réf.	UV.	EUR/pièce HTVA	SP	EAN
 blanc crème brillant	2101 01	1	152,70	06	4010337048183
 blanc brillant	2101 03	1	152,70	06	4010337048190
 blanc satiné	2101 27	1	152,70	06	4010337048244
 anthracite	2101 28	1	154,74	06	4010337048251
 teinte alu	2101 26	1	156,77	06	4010337048237
 noir mat	2101 005	1	156,77	06	4010337037248
 gris mat	2101 015	1	156,77	06	4010337083030
 acier inoxydable	2101 600	1	158,81	06	4010337021513

### Caractéristiques techniques

Profondeur de montage: 23 mm

## Indications

- Le régulateur de bâtiment ne possède pas d'éléments de commande ou d'affichage.
-