









Regolatore continuo con interfaccia pulsanti 4 moduli per KNX



Specifica	Cod. ord.	UI	EUR/pezzo IVA esclusa	SP	EAN
 bianco crema brillante	2100 01	1	353,15	06	4010337048022
 bianco puro brillante	2100 03	1	353,15	06	4010337048039
 bianco puro satinato	2100 27	1	353,15	06	4010337048060
 antracite	2100 28	1	355,79	06	4010337048077
 color alluminio	2100 26	1	360,07	06	4010337048053
 nero opaco	2100 005	1	360,07	06	4010337037255
 grigio opaco	2100 015	1	360,07	06	4010337083016
 acciaio inox	2100 600	1	367,60	06	4010337021520

Caratteristiche

- Con la manopola si modifica il valore nominale della temperatura.
- Un pulsante di presenza serve a commutare tra il servizio Comfort e stand-by.
- Gli stati correnti vengono visualizzati tramite LED sul regolatore continuo.

Dati tecnici

Profondità di montaggio: 23 mm
