










Objectregelaar met drukcontactinterface 4-voudig voor KNX



Specificatie	Art. nr.	VE	EUR/stuk excl. BTW	PS	EAN
 crème wit glanzend	2101 01	1	152,70	06	4010337048183
 zuiver wit glanzend	2101 03	1	152,70	06	4010337048190
 zuiver wit mat	2101 27	1	152,70	06	4010337048244
 antraciet	2101 28	1	154,74	06	4010337048251
 kleur aluminium	2101 26	1	156,77	06	4010337048237
 zwart mat	2101 005	1	156,77	06	4010337037248
 grijs mat	2101 015	1	156,77	06	4010337083030
 edelstaal	2101 600	1	158,81	06	4010337021513

Technische gegevens

Inbouwdiepte: 23 mm

Aanwijzingen

- De objectregelaar heeft geen bedienings- of weergave-elementen.
