








Kontinuerlig regulator med trykknappgrensesnitt 4-dobbel for KNX



Spesifikasjon	Bestillings nr.	PE	PS	EAN
 kremhvit glans	2100 01	1	06	4010337048022
 renhvit glans	2100 03 4504031	1	06	4010337048039
 antrasitt	2100 28 4504035	1	06	4010337048077
 aluminiumsfarget	2100 26 4504033	1	06	4010337048053
 svart matt	2100 005 4505174	1	06	4010337037255
 grå matt	2100 015	1	06	4010337083016
 rustfritt stål	2100 600	1	06	4010337021520

Egenskaper

- Den nominelle temperaturverdien forskyves med reguleringshjulet.
- En tilstedeværelsesknapp brukes til omkobling mellom komfort- og beredskapsmodus.
- De aktuelle tilstandene vises av LED-er på den kontinuerlige regulatoren.

Tekniske data

Monteringsdybde: 23 mm
